



Multi Display Manager MDM-1-EL (Entry Level)





- **9 video inputs**
- **Supports UHD input signal**
- **Support of one 8MP or two 4MP Displays**
- **Real-time architecture with low latency**
- **Customer definable screen arrangements**
- **Hardware scaling with bilinear filter for best possible video quality**
- **High reliable design with redundancies & watch dog build for 24x7 operations**
- **On-Screen administration tool & API for remote control & Touch PanelPC support**
- **Multiple User KVM functionality fully integrated**



Overview

- MDM contains **all system functionality** in **one unit**
- Capability to collect, combine, and transmit **9 different video sources** on **1x 8MP QFHD@60Hz** or **2x 4MP** displays.
- one **UHD input** signal with 550MHz pixel clock
- **Digital and analog** (with ADIO-1) inputs are supported.
- 2-3 frames delay from input to display possible because of a **Real-time architecture**
- Customer **definable size, position** and **scale** of sources, **including overlapping**.
- Sources can be **cropped** on top, bottom, left or right
- Signal can be **scaled** by a factor of 0.1 to 10.0.
- Signals can be **duplicated** to show the same input, cropped or sized on one of different outputs
- Sources can be **framed** (borders with selectable colours and thickness) and **named** (font, color, size and position definable)
- **Customer definable arrangement** sets that can be easily switched via Touch PanelPC, web-interface with iPad or similar device.
- Arrangements are storable at the system as well as external storage equipment.
- Switching between predefined arrangement sets is less then 500ms
- In **critical environments**, the MDM has a highly **reliable design**. No hard disk is used; Redundant FANs; and Active Watch Dog are employed
- **Robust construction** and material methods employed for use in specialized Medical and Industrial disciplines **build for 24x7 operations**.
- **Status information** and Diagnostics accessible **via network**.
- **Customizing** for OEM partners is available.





In total 2 connectors can be used with: max. 1x 8MP or 2x 4MP¹

Output displays with the same resolution are configurable not only as independent displays, but also as extended displays. The behaviour is like an extended desktop on a local PC and two attached monitors.


(1) MDM Display Port to Dual Link DVI Converter necessary.

<i>Type</i>		MDM-1-EL
Maximal Display Resolution		8MP (max. 600MHz)
Number of Output connections ⁽¹⁾		2x DisplayPort 1.2
<i>MDI-7 input boards</i>		
Number of Inputs		9
Number of Digital Inputs [HDMI] [550MHz]		1
Number of Digital Inputs [HDMI] [165MHz]		4
Number of Digital Inputs [DVI (HDMI)] [165MHz]		4
Support of Analog Inputs [165MHz]		with ADIO-1 Extension Box
Videotiming	H-Display	Min. 320 Pixel ↔ Max. 4096 Pixel
	V-Display	Min. 200 Lines ↔ Max. 2560 Lines
	Pixel-Clock	Min. 16MHz ↔ Max. 165/550MHz
	H-Blank	Min. 8 Pixel
	V-Blank	Min. 4 Lines
	Interlace	Not supported, progressive timings only
Bandwidth	per System	1.200MPx/s
<i>Inputs with MDI-5 input boards</i>		
Number of Inputs		9
Number of Digital Inputs [DVI (HDMI)] [165MHz]		6
Number of Digital Inputs [DVI-I] [165MHz]		1
Number of Analog Inputs [DVI-I] [135MHz]		1
Number of Analog Inputs [VGA] [170MHz]		1
Videotiming	H-Display	Min. 320 Pixel ↔ Max. 2048 Pixel
	V-Display	Min. 200 Lines ↔ Max. 2560 Lines
	Pixel-Clock	Min. 16MHz ↔ Max. 140/165/170MHz
	H-Blank	Min. 8 Pixel
	V-Blank	Min. 4 Lines
	Interlace	Not supported, progressive timings only
Bandwidth	per System	620MPx/s

TRITEC is offering a wide range of equipment completely validated and certified to work with our Multi Display Manager Video Processor. Begins with high quality cabling with locks, HD-SDI converter, optical extenders with galvanic isolation, any many more.



MDM-1-EL



Option Bay Upgrades

- KMS-1 Board and/or
- PPB Board

MDM-1 Options	
MDI Input Boards	
Downgrade to MDI-5 Boards	Replace preconfigured MDI-7 Boards with a MDI-5 Boards to add analog inputs directly to the MDM.
Add-Ons (check maximum available option bays on next page)	
KMS-1 Board	7 Port Keyboard/Mouse Switch module, USB to Host connection
PPB-S Board	7 Port 5V Power Breakout Module; provides external 5V power (Hirose)

Differences between MDM-EL and MDM Model D		
	MDM-EL	MDM-Model-D
max. Displays	1x 8MP or 2x 4MP	5
Connection Type	1x DP 1.2 or 2x DL-DVI ¹	1x DP 1.2, 2x DL-DVI ¹ 4x HD ²
KVM	2x Displays	4x Displays
max. No. of Inputs	9	23
Mirroring	No	Yes
Standby	No	Yes
Redundant Power Supply	No	Yes

- (1) MDM Display Port to Dual Link DVI Converter necessary.
- (2) Adapters necessary.




MDM-1-EL w KMS and PPB

The Multi Display Manager supports multiple ways of configure and control the device.


External Browser Interface

A full featured configuration WebApp is provided by the MDM by its internal LAN Interface.




OnScreen Interface

The Multi Display Manager is able to show the configuration WebApp as a single window OnScreen. It is usable by connecting a Keyboard and Mouse beneath a display to the MDM




REST Interface

The REST Interface provides OEM partners to fully integrate the configuration of a MDM into their management environment. A well documented and standardized interface language keeping implementation efforts on a very low level.



Touch Panel PC

The latest development is a network attached Touch PanelPC which is able to switch the layout of a display which is attached to a Multi Display Manager. It is possible to have multiple Touch Panel PC connected to one MDM.



Power Supply		Environmental Specifications	
non redundant 400W		Unpackaged Operating	Temperature 5 °C according EN 60068-2-1
Input Voltage	90 - 264VAC		Temperature 40 °C according EN 60068-2-2.
Input Frequency	47 to 63Hz	Unpackaged Operating Humidity	Damp heat, 25°C, 10 to 80% RH (non condensing) according EN 60068-2-38.
Inrush Current	20A max. @115VAC / 40A max. @230VAC		Unpackaged Operating Pressure
Isolation	3100VAC	Packaged Non-Operating Temperature (Storage, Transportation)	
Leakage Current	<1.5mA		Temperature +70°C according EN 60068-2-2.
Input Connector	EC320/C14	Packaged Non-Operating Humidity	+25°C 10 to 95% RH (non-condensing) according 60068-2-38.
Efficiency	>80%		Packaged Non-Operating Pressure
Input Current	Max. 6A@115VAC / 3A @ 230VAC Typ. 3A@115VAC / 1.5A@230VAC	Packaged Tests Continuous Shock	
Power Consumption	Typ. 340W		Package Drop Test
Power switch	Power switch at the back, no other hardware power off/on switch.	Degree of protection	
Electrical Safety & EMC Specifications		Dimensions	
Electrical Safety:	Power supply according EN62368, UL62368, IEC62368	Model	MDM-1-EL
EMC:	According EN55022 and EN55024.	Chassis	19" 4U Desksite
Radiated Emissions:	IEC61000-3-2/EN61000-3-2 (Harmonic Current Emissions)	Size unpacked (WxHxD)	483x177x500mm 175x440x575mm
	IEC61000-3-3/EN61000-3-3 (Voltage Changes) CISPR 22/ EN55022 or CISPR 11/ EN55011 Level B Radiated & Conducted Emissions. FCC class A.	Weight unpa.	15kg 16kg
Immunity:	IEC61000-4-2/EN61000-4-2 Level 2 (ESD)	Size packed (WxHxD)	800x460x800mm 800x460x800mm
	IEC61000-4-3/EN61000-4-3 Level 2 (EM Field Immunity)	Weight pack.	24kg 25kg
	IEC61000-4-4/EN61000-4-4 Level 2 (Fast Transient/Burst Immunity)	Other Inputs / Outputs	
	IEC61000-4-5/EN61000-4-5 Level 2 (Surge Immunity)	Networking:	Ethernet 10/100/1000Mbit/s
	IEC61000-4-6/EN61000-4-6 Level 2 (Conducted Disturbances)	Connector RJ45	
	IEC61000-4-8/EN61000-4-8 Level 2 (Power Freq Magnetic Immunity)	USB	2x KVM Support 2x Power DP-Converter
	IEC61000-4-11/EN61000-4-11 Level 3 (Voltage Dips, Short Interrupt, Voltage Variations Immunity).	Other	All other inputs/outputs should not be connected.
Marking	CE, FCC, RoHS, UL, WEEE		
Reliability			
MTBF	55.000h		

ADIO-1 Extension Box

Video signal repeater and converter with one device only.



Order Number	Optical Isolation	Output Connector	Repeater Outputs	Inputs	Packaging list
ADIO-1H-AH	No	HDMI	yes	HDMI, VGA, analog	ADIO-1H TX Unit
ADIO-1H-AHDUS	No	HDMI	yes	DVI, DP, HDMI, VGA, analog, USB, SDI	ADIO-1H-AHDUS TX Unit
ADIO-1H-VHDS	No	HDMI	no	DVI, DP, HDMI, VGA, SDI	ADIO-1H-VHDS TX Unit
ADIO-1O-AH	yes	HDMI	yes	HDMI, VGA, analog	ADIO-1H TX Unit, Optical Bundle ₁
ADIO-1O-AHDUS	yes	HDMI	yes	DVI, DP, HDMI, VGA, analog, USB, SDI	ADIO-1H-AHDUS TX Unit, Optical Bundle ₁
ADIO-1O-VHDS	yes	HDMI	no	DVI, DP, HDMI, VGA, SDI	ADIO-1H-VHDS TX Unit, Optical Bundle ₁
ADIO-1-PSU	Power supply				One power supply with adapter cable

(1) Optical bundle includes: Power Supply for ADIO unit, optical transmitter, 36m Optical Cable, Optical Receiver, cable to supply Optical Receiver with power from MDM Power Break Out Board, cable to connect the Optical Receiver to the MDM HDMI input connector with lock.



Europe

TRITEC Electronic GmbH
Carl-Zeiss-Strasse 41
55129 Mainz, Germany
www.tritec.de

America

The Linden Group Corp.
2B Wing Dr.
Cedar Knolls, NJ 07927, USA
www.optikview.com

Worldwide Sales

OEM, distribution and reseller requests are welcome. Please contact TRITEC for more information.



Copyright 2022 TRITEC Electronic GmbH

All rights reserved. Copyright in the documents is owned by TRITEC Electronic GmbH. This publication is provided “as is” without warranty of any kind, either express or implied, including, but not limited to, the implied warranties of merchantability, fitness for a particular purpose, or non-infringement. This publication could include technical inaccuracies or typographical errors. Changes are periodically added to the information herein; these changes will be incorporated in new editions of the publication. TRITEC may make improvements and/or changes in the product(s) and/or the program(s) described in this publication at any time. Specifications subject to change without notice.

TRADEMARKS

TRITEC, TRIstation, neTRI, TRITEC logo, Multi Display Manager are trademarks or registered trademarks of TRITEC Electronic GmbH. All other product names mentioned herein are the trademarks of their respective owners.

TRITEC Electronic GmbH

Carl-Zeiss-Str. 41
55129 Mainz, Germany
Tel. +49 6131 92 22-0

Fax +49 6131 92 22-29
E-Mail: sales@tritec.de
URL: <http://www.tritec.de>

